

**Specifications:-**

- The Unit Consists Of Two Movable Frames Pivoted At One End.
- The Extensometer Is Fixed To The Specimen With The Help Of Tightening Screws.
- The Lateral Extension Is Indicated On A Dial Gauge Of 0.002 mm X 12 mm Travel.
- The Extension Is Magnified 2.5 Times And The Dial Gauge Readings Are To Be Divided By 2.5 To Get The Exact Readings.
- A Spacer Strip Is Provided To Initially Set The Dial Gauge And Can Be Removed After Initial Setting.
- Supplied In A Wooden Carrying Case.

Note: Specifications are subject to change, Photos shown above are Indicative, Actual Product can Vary.



Export Sales: +91-9829132777
India Sales: +91-9588842361



IT-2013, Ramchandrapura Industrial Area,
Sitapura Extension, Jaipur-302022, India.



info@tesca.in
www.tescaglobal.com