

**Specifications:-**

- Spectrum Discharge Tube With Molecular Hydrogen (H<sub>2</sub>) As Its Gas. One Of A Series Of Gas Tubes That Show Spectral Lines Of Pure Substances. For Intermittent Use Only, Not To Be Used As A Lamp Source.
- Designed To Operate 30 Seconds On - 30 Seconds Off
- Spectroscopy Tube Length Is Approx. 26 Cm.
- Cardboard Box And Wooden Box

*Note: Specifications are subject to change, Photos shown above are Indicative, Actual Product can Vary.*



Export Sales: +91-9829132777  
India Sales: +91-9588842361



IT-2013, Ramchandrapura Industrial Area,  
Sitapura Extension, Jaipur-302022, India.



info@tesca.in  
www.tescaglobal.com