



Features

- Function & identification of Electro-pneumatic components & their symbols.
- Direct and indirect manual controls, stroke dependant controls, time dependant and pressure dependant controls with time delay, pressure sequence valves.
- Design & function of a electro-pneumatic System.
- Functional diagrams.
- Logic AND/OR function to start signals.
- Application and fault findings of Electro Pneumatic controls.
- Pneumatic power section – Electric control section.
- To empower students to design their own circuits.
- The kit is modular and upgradable.
- Training literature – Instruction & operation manual , troubleshooting & maintenance tips will be provided in soft copy as well as hard copy format

Objectives

- The components are capable of being mounted on an appropriate profile plate with grooves for secure and flexible positioning so that the components can be clamped firmly, quickly and safely through quick fix adaptors. Industrial components are used in the kit so that the students get hands on practical training in using

Experiments

- Study of Advanced Electro – Pneumatic Trainer.
- Study of Self Reciprocation of Single Acting Cylinder by Using Electric Limit Switch & 3/2 Solenoid Valve
- Study of Self Reciprocation of Double Acting Cylinder by Using Proximity Switch & 5/2 Double Sided S.V.
- Study of Self Reciprocation of Double Acting Cylinder by Using Proximity Switches & 5/2 Single Sided S.V.
- Study of AND Valve (Dual Pressure Valve)
- Study of Shuttle Valve (OR Valve) Study of Quick Exhaust Valve
- Study of operation of Hand Lever Valve (3/2 & 5/2 DCV) Study of operation Of 5/2 Push Button Valve
- Study of operation Of 3/2 Single Pilot Operated Valve Study of Pressure Sequence Valve
- Study of Flow Control Valve & Pneumatic Motor Study of P To E Converter
- Study of using Signal Input Electrical Box , Relay Three Fold, Indicator & Distributor Unit
- Study of Pneumatic & Electro-Pneumatic Circuits.
- Study of PLC Based cylinder position sensing & Actuation of Solenoid Valves (Optional)
- Study of Time Delay Valve
- Study of Electronic Timer (Optional)
- Study of Operation of Pneumatic Simulation Software (SCADA) (Optional)

Note: Specifications are subject to change.

Tesca Technologies Pvt. Ltd.

IT-2013, Ramchandrapura Industrial Area, Sitapura Extension,
Near Bombay Hospital, Vidhani Circle, Jaipur-302022, Rajasthan, India,
Tel: +91-141-2771791 / 2771792; Email: info@tesca.in, tesca.technologies@gmail.com
Website: www.tescaglobal.com

Technical Specification		
No.	Item Name	Technical Specifications
1	Profile Plates & Stand-	The anodized Aluminum profile plate is the basis for training. All components fit securely & safely onto the profile plate with safe fixing arrangement ,Grid Dimensions: 50mm, Size: 1000 ×700mm
2	Shuttle Valve (OR)-	Make: JELPC/Eqvt 1 No., The Shuttle Valve is switched through to the output by applying compressed air to one of the inputs (OR) function. Design type is OR gate (shuttle valve).Pressure range: (1-10 Bar)
3	Dual Pressure Valve (AND)-	Make: JELPC/Eqvt 1 No., the dual-pressure Valve is switched through to the output by applying compressed air to both the inputs (AND) Function. Design type is AND Gate (Dual Pressure Valve). Pressure Range: (1-10 Bar)
4	One way flow Control Valve Assembly-	Make: JELPC/Eqvt 1 No., the One - way flow control valve is a combination of flow control valve & a non-return valve. The cross section of the restrictor can be set by means of a Knurled screw. Design type is combined flow control Valve. Pressure range – (0.5-10 Bar)
5	Pressure Sequence Valve assembly-	Make: JELPC/Eqvt 1 No., The pressure of the control signal can be set by means of the pressure setting screw (variable). Design type is Poppet Valve with return spring, Operating Pressure range – (1.8 – 8 bar). Control Pressure range - (1 – 8 bar)
6	Single Acting Cylinder-	1 No. : Design type is Piston Cylinder. Operating Pressure 10 bar. Stroke length–100mm
7	Double Acting Cylinder-	Design – Piston Cylinder. Operating Pressure – 10 bar, Stroke Length – Max 100mm
8	Manifold Assembly-	1 No., Manifold with 6 (2 ×3) Hex-Ball Valve. A common manifold for plastic tubing allows supply of compressed air to the control via six individual ports (for plastic tubing PUN 4×0.75)
9	Filter regulator with	Filter control valve with pressure gauge, gate valve, quick push-pull connectors Gauge-& quick couplings mounted on a swivel support. The filter with water separator removes dirt, pipe sinter, rust & condensed water. The pressure control valve regulates the supply. Air pressure to the set operating pressure & compensates pressure fluctuations. The filter bowl has a condensate drain valve. The shutoff valve ventilates & vents entire control. Input pressure –Maximum (16 bar),Output pressure – Max 12 bar, grade of filtration– 40 mm approx., Connector – G 1/8 , / PU 4
10	Relay, Three fold-	1 No., the device has three relays with terminals and two buses for power supply. Contact set – Single change-over switches, Contact load – maximum 5 A
11	Signal Input, Electrical-	1 No., The device contains an illuminated push-button switch (control switch) & two illuminated push buttons (momentary contact switches) with terminals & two buses for power supply. Contact set- 2 makes, 2 breaks, Contact load- max 1A.
12	Indicator & Distributor Unit, electrical-	1 No., The device contains an acoustic indicator and four lamps with terminals and three buses for power supply. Through-contact socket pairs per lamp allow the element to also be used as a Distributor.
13	Proximity switch with attachment-	2 No. : The Proximity switch consists of a sensor, the mounting kit and the cable. This proximity switch gives a signal when it detects a metal. The status is indicated by an LED. Switching Voltage – 24 VDC, Switching current – max. 200 mA, Switching Power – 6 W approx, switching accuracy - ±0.1mm
14	Equipment Tray-	1 No., MS powder coated tray with slots for placing components to be supplied with Electro-pneumatic supplementary kit.

Note: Specifications are subject to change.

Tesca Technologies Pvt. Ltd.

IT-2013, Ramchandrapura Industrial Area, Sitapura Extension,
Near Bombay Hospital, Vidhani Circle, Jaipur-302022, Rajasthan, India,
Tel: +91-141-2771791 / 2771792; Email: info@tesca.in, tesca.technologies@gmail.com
Website: www.tescaglobal.com

Technical Specification		
No.	Item Name	Technical Specifications
15	5/2 way single sided	1 No., The status is indicated by an LED on the housing. The valve is equipped Solenoid Valve with LED-with a manual override. Pneumatic Technical data: Design type is spool valve, pilot controlled with return spring, Pressure range: 250-800 KPa (2.5-8 bar), lectrical Technical data: Power consumption – 1.5 W
16	5/2 Solenoid Valve,	1 No., The statuses are indicated by LEDs on the housings. The valve is equipped Double sided with LED-with two manual overrides. Pneumatic Technical Data: Design-spool valve with pilot control, Pressure range – 150-800KPa (1.5-8 bar) Electrical Technical Data: Power Consumption – 1.5 W
17	Pneumatic – Electric	1 No., The pneumatic – electric convertor can fulfill 3 functions: Pressure convertor-Switch, Vacuum Switch and Differential Pressure Switch. Pneumatic Technical Data- Pressure Ranges: Pressure Switch connector, P1: 0.25 to 3.5bar, Vacuum Switch: -0.2 to -0.8 bar, Differential Pressure Switch: Connector, P2 - (-0.95 to 3.5 bar)
18	Limit Switch, Left	1 No., The electrical limit switch comprises a mechanically operated micro-Actuated-switch. When the roller lever is pressed, for example, by control cam of a cylinder, the micro-switch is actuated. The circuit is closed or opened via the contacts. The micro-switch can be wired as a normally open or normally closed or changeover contact. Contact load: maximum 5A, switching frequency: maximum 200Hz, Reproducible accuracy: 0.2mm, Switch travel: 2.7 mm, Actuator force: 5N
19	Limit Switch, Right	1 No., The electrical limit switch comprises a mechanically operated micro-actuated-switch. When the roller lever is pressed, for example, by control cam of a cylinder, the micro-switch is actuated. The circuit is closed or opened via the contacts. The micro-switch can be wired as a normally open or normally closed or changeover contact. Contact load: maximum 5A, switching frequency: maximum 200Hz, Reproducible accuracy: 0.2mm, Switch travel: 2.7 mm, Actuator force: 5N
20	Plug in adapter-	For mounting components with plug-in foot on the aluminum profile plate.
21	Power Supply Unit-	1 No., Input Voltage: 230 / 115 VAC (47 - 63 Hz.), Output Voltage: 24 V DC, short circuit proof, output current: Max. 4.5 A, Connection Cable – 3m
22	3/2 Solenoid Valve, Single with LED-	1No.: The status is indicated by an LED on the housing. The valve is equipped with a manual override. Pneumatic Technical data: Design type is spool valve, pilot controlled with return spring, Pressure range : 250-800 kPa (2.5-8 bar), Electrical
23	Quick Push-Pull connectors-	Sufficient shall be supplied for branching of the tubing for making of the circuitry
24	Plastic Tubing-	PUN 4×0.75, Exterior Diameter-6mm, Interior Diameter- 4mm, Transparent – 10mtrs/Blue-10mtrs
25	Set of molded Cables-	1.5 Meter (2 core) - 4 No. 1.5 Meter (3 core) - 3 No. 1.5 Meter (1 core): Red- 05 Nos, Black- 05 Nos. BS5 Patch cords: Red - 5 Nos.(Approx. 300mm), Black - 5 Nos.(Approx.300mm)
26	Hand Lever Operated Valve	3/2 Hand Lever Operated Valve -1 No. & 5/2 Hand Lever operated Valves-1 No. each Connection: ¼" Connection. Design type is spool valve. Actuation using Hand Lever.
27	5/2 Push Button Operated Valve	1 No. Connection: ¼" Connection. Design type is spool valve. Actuation using Push Button.
28	Quick Exhaust Valve	1 No. Connection: ¼" Connection
29	Pneumatic Motor	Unidirectional, Air pressure: 0-90 psi.
30	3/2 Pilot operated valve	3/2 way Valve, ¼" Connection


Note: Specifications are subject to change.

Tesca Technologies Pvt. Ltd.

IT-2013, Ramchandrapura Industrial Area, Sitapura Extension,
Near Bombay Hospital, Vidhani Circle, Jaipur-302022, Rajasthan, India,
Tel: +91-141-2771791 / 2771792; Email: info@tesca.in, tesca.technologies@gmail.com
Website: www.tescaglobal.com

Technical Specification

No.	Item Name	Technical Specifications
31	PLC Panel (Optional)-	Make: Siemens Logo / A-B MICRO 810 Equivalent, Digital Input: 8, Digital Output: 4, Input / Output LED indication on front Facia of the panel.
32	Time Delay Valve-	1 No. Connection: ¼" Connection
33	Electronic Timer (Optional)-	1 No., Power Supply -24VDC with C,NO,NC terminals
34	Air Compressor (Optional)-	Tank capacity: 25 Liters, Discharge: 2 CFM, Motor: 1 H.P. 230 V AC Operated, Working Pressure: 5-6 kg/cm2
35	Pneumatic Simulation Software (Optional)	



Note: Specifications are subject to change.

Tesca Technologies Pvt. Ltd.

IT-2013, Ramchandrapura Industrial Area, Sitapura Extension,
Near Bombay Hospital, Vidhani Circle, Jaipur-302022, Rajasthan, India,
Tel: +91-141-2771791 / 2771792; Email: info@tesca.in, tesca.technologies@gmail.com
Website: www.tescaglobal.com