

Specifications:

- DC power supply 0-60 volt 8 ampere with 3 digit LED display
- Four line LCD display to indicate the current in all the six cell's current in milli ampere.
- · Built in data acquisition system with PC interface software

The total Supply includes the following components:

- SIX Cell RCPT apparatus, current six of three cells with PC interface software
- Acrylic Cells Machined as per ASTM C 1202 to hold the concrete specimens of 100 mm diameter 6 sets
- Flexible cable 1 meter long with banana connectors- Red 6 nos.
- Flexible cable 1 meter long with banana connectors- Black 6 nos.
- RS232- USB port interface cable 1 no.
- Software CD 1 no.
- Stainless Steel Bolts 24 Nos.
- Stainless steel washers 48 nos. .
- Stainless steel Nuts 48 nos.
- RTV sealant 1 tube
- GUN
- 300 mm vacuum desiccators. 1 No.
- Vacuum pump 1 No.
- Moisture trap with vacuum gauge 1 No.
- Elastomeric Rubber Moulds for cylindrical specimens 6 Nos.

Consumables:

- NaOH salt 500 gram
- NaCl salt 500 gram
- Acrylic cell consists of the followings:
- Brass mess -88mm diameter 1 no
- Brass plate -88mm diameter 1 no
- Brass washer- 102 mm OD 88mm ID 1 no
- Rubber washer 102mm OD 88 mm ID 1 no

Note: Specifications are subject to change.

C **Tesca Technologies Pvt. Ltd.** C IT-2013, Ramchandrapura Industrial Area, Sitapura Extension,

Hear Bombay Hospital, Vidhani Circle, Jaipur-302022, Rajasthan, India,

Tel: +91-9829132777; Email: info@tesca.in, tesca.technologies@gmail.com

⁴ Website: www.tescaglobal.com