

**Features:-**

- Convenient and easy operate on 5.6" touch screen
- Both Central and individual pressure can be achieved
- Electrical connections for 4 groups of dosing/stirring system
- Contains 21 groups of commonly used grinding programs, customized programs also can be saved
- Large diameter of drain hose
- Replaceable wheel design makes easy to clean and maintenance
- The automatic temperature-sensing cooling fan, can reduce failure rate and improve working life
- Retractable water spout.

Note: Specifications are subject to change, Photos shown above are Indicative, Actual Product can Vary.



Export Sales: +91-9829132777
India Sales: +91-9588842361



IT-2013, Ramchandrapura Industrial Area,
Sitapura Extension, Jaipur-302022, India.



info@tesca.in
www.tescaglobal.com

Technical Specifications:-

Head	Force Application	Central and Individual
	Central Force	20- 500N
	Individual Force	5- 100N
	Power	400W
	Speed	20~150rpm
	Direction	CCW
Grinder	Power	750W
	Grinder Speed	50- 750rpm
	Wheel Diameter	8"- 10"- 12"(200/250/300mm).
	Direction	CW/CCW
Dosing System	Pump	Max. flow: 52ml/min
	Pump numbers	With 2 stirring motors
Specimen holder	Individual pressure	Standard 6xΦ30mm(6xΦ25mm,6xΦ 40mm,6xΦ50mm Optional)
	Central pressure	Standard 6xΦ30mm(6xΦ25mm,6xΦ 40mm,6xΦ50mm Optional)
Operating Environment	Temperature	-20°C - 60°C
	Humidity	0-95%RH
Dimension	WxDxH	660×730×630mm
Weight		80kg

Control Panel Introduction:-



Home Screen:

- ❶ Procedures selection
- ❷ Automatic mode (Run selected procedure)
- ❸ Manual mode
- ❹ Parameters settings

Note: Specifications are subject to change, Photos shown above are Indicative, Actual Product can Vary.



Export Sales: +91-9829132777
India Sales: +91-9588842361



IT-2013, Ramchandrapura Industrial Area,
Sitapura Extension, Jaipur-302022, India.



info@tesca.in
www.tescaglobal.com