



Key Features

- In this apparatus, a hook is provided to one end of powdered coated bar having dimension $100 \times 1.8 \times 0.3$ cm (L×B×W). The whole metallic bar is marked with lines. All lines are separated from each other a distance of 5cm. The cantilever bar is held horizontally keeping breath in horizontal position.

SCOPE OF LEARNING:

- Determination of Young's Modulus 'Y' of a bar by bending.

REQUIRED ACCESSORIES

- Cantilever apparatus
- Slotted weight, Cast Iron, set of 5, with hanger, 500g each
- G Clamp

Note: Specifications are subject to change, Photos shown above are Indicative, Actual Product can Vary.



Export Sales: +91-9829132777
 India Sales: +91-9588842361



IT-2013, Ramchandrapura Industrial Area,
 Sitapura Extension, Jaipur-302022, India.



info@tesca.in
 www.tescaglobal.com